

# LET'S CONNECT

■■■■ PRINECT ■■  
USER DAYS

# Prinect CR Production — UPDATE

# Safety first!



\*one issue with Signa Pack Pro



for new installations first



# Prinect CR Production – Update

## 1. Safety first!

## 2. Device connectivity:

CMM Workflow for Jetfire50  
Feature sets for Inspection Control 4  
& Plate-to-Unit workflows

## 3. Also new:

European Data Act (EDA) compliant  
Prepared for  
European Deforestation Regulation (EUDR)  
PDF Processing – e.g. application dependent „refry“,  
postage paid, ...

## 4. HEIDELBERG Customer Portal:

Color Quality Reports  
Inspection Reports



## 2 Prinect CR. Proofers added



coming with Color Proof Pro 9.0

**Epson**

**SC-P 7300**

**SC-P 9300**

### ▼ Color Proof Pro

CR

2021.10 (8.0.X)

2021.10 (7.3.X)

2021.10 (7.1.X)

[Color Proof Pro Device list \(PDF\)](#)



since Color Proof Pro 8.04

**Canon imagePROGRAF**



TM-240 RGB

TM-250 RGB

TM-255 RGB

TM-340 RGB

TM-350 RGB

TM-355 RGB

TM-5240 RGB

TM-5250 RGB

TM-5255 RGB

TM-5340 RGB

TM-5350 RGB

TM-5355 RGB

TX 3200 CT

TX 3200 RGB

TX 4200 CT

TX 4200 RGB

TX 5220 CT

TX 5220 RGB

TX 5320 CT

TX 5320 RGB

TX 5420 CT

TX 5420 RGB

TZ 32000 CT

TZ 32000 RGB

TZ 5320 CT

TZ 5320 RGB

## Video Set "Did You know ...?"

Watch our new set of short videos with lots of useful tips on Prinect applications.

**Note:** Subtitles can be switched between various languages.

12/10/2025

### **New Rules for Restriction to Sujet or Paper Size**

**Duration: 2:27 ►**

Keywords:

Signa Station, Automarks, Rules, Plate template, Reducing touch points

11/26/2025

### **Color Handling – Alias Assignment is now Case-Sensitive**

**Duration: 1:13 ►**

Keywords:

Cockpit, Marks assignment, MIS, Inkprofile

11/04/2025

### **Stop Jobs With Wrong Colors**

**Duration: 2:21 ►**

Keywords:

Cockpit, AutoSheet, MIS, PrePress

10/15/2025

### **Duplicate Cutting Dies**

**Duration: 0:58 ►**

Keywords:

Signa Station, Margins, Rotation

10/01/2025

### **Automark "Linetype Covermark" in Packaging Jobs**

**Duration: 2:17 ►**

Keywords:

Signa Station, Packaging, Glue flaps, Dust flaps

10/01/2025

### **Different Bleed on Front and Back with Packaging Pro**

**Duration: 4:11 ►**

Keywords:

Signa Station, Important Area, Resolve Conflicts

09/01/2025

### **Quick Search in Signa Station**

**Duration: 1:00 ►**

Keywords:

Search Field, Resources, Choose Paper Dialog

# Prinect CR Production – Update

## 1. Safety first!

## 2. Device connectivity:

CMM Workflow for Jetfire 50  
 Feature sets for Inspection Control 4  
 & Plate-to-Unit workflows  
 Additional Proofers

## 3. Also new:

European Data Act (EDA) compliant  
 Prepared for  
 European Deforestation Regulation (EUDR)  
 PDF Processing – e.g. application dependent „refry“,  
 postage paid, ...

## 4. HEIDELBERG Customer Portal:


Color Color Quality Reports  
 Inspection Reports



## 5. Multidot – One year after PUD 25



# Multidot customers worldwide: 79






# Some customer Feedback – Multidot in Prepress saves ink while printing

UK



## Average ink consumption

- **0,71 kg per 1000 sheets before**  
(the 7 months before implementation)
- **0,57 kg per 1000 sheets WITH Multidot**  
(the 11 months after implementation)



## More customer feedback on ink saving – and quality

### Japan



- **Prinect Multidot** screen was the **deciding factor to switch to Prinect** from a competitive prepress workflow.
- Since the changeover, our customer has been printing on four 8-colour offset presses with Multidot and
  - **saved more than 15% ink in total.**

(= more than US\$ 200,000 @ statement date)

### Sweden




- Customer statement:

“When using Multidot on carton with images, or on other types of print jobs like books on standard paper, the benefits are clear

— **faster to OK sheet, wide color gamut, and excellent detail reproduction.”**

# New print sample folder soon available via your sales organization

## PRINT SAMPLES



OF DIFFERENT SCREENING  
SYSTEM MULTICOLOR  
SEPARATION PRINTS

- Prints of **7-color-separations**

screened with

**AM + FM mixed screening**

**Multidot screening**

**FM screening**



